




Altavoz para la radio empotrable



| Especificación | Ref. | UE | SP | EAN |
|--|----------|----|----|---------------|
|  blanco crema brillante | 2282 01 | 1 | 03 | 4010337076230 |
|  blanco brillante | 2282 03 | 1 | 03 | 4010337076247 |
|  blanco mate | 2282 27 | 1 | 03 | 4010337076254 |
|  antracita | 2282 28 | 1 | 03 | 4010337076261 |
|  color aluminio | 2282 26 | 1 | 03 | 4010337076162 |
|  aspecto de cristal negro | 2282 05 | 1 | 03 | 4010337889182 |
|  negro mate | 2282 005 | 1 | 03 | 4010337037286 |
|  gris mate | 2282 015 | 1 | 03 | 4010337083931 |
|  acero inoxidable | 2282 600 | 1 | 03 | 4010337032861 |

Características

- Altavoz para la conexión a la radio empotrable Gira.

Datos técnicos

| | |
|---|---------------------|
| Profundidad de instalación: | 32 mm |
| Sección de conexión - Conexión de altavoces/AUX: | 1,5 mm ² |
| Impedancia: | 8 Ω |
| Temperatura ambiente: | de -5 °C a +50 °C |
