







## Altavoz para la radio empotrable



Especificación	Ref.	UE	SP	EAN
 blanco crema brillante	2282 01	1	03	4010337076230
 blanco brillante	2282 03	1	03	4010337076247
 blanco mate	2282 27	1	03	4010337076254
 antracita	2282 28	1	03	4010337076261
 color aluminio	2282 26	1	03	4010337076162
 aspecto de cristal negro	2282 05	1	03	4010337889182
 negro mate	2282 005	1	03	4010337037286
 gris mate	2282 015	1	03	4010337083931
 acero inoxidable	2282 600	1	03	4010337032861

## Características

- Altavoz para la conexión a la radio empotrable Gira.

---

## Datos técnicos

Profundidad de instalación:	32 mm
Sección de conexión - Conexión de altavoces/AUX:	1,5 mm <sup>2</sup>
Impedancia:	8 Ω
Temperatura ambiente:	de -5 °C a +50 °C

---