








**Interruptor pulsador 10 AX de 250 V~con tecla basculante recta de 2 elementos  
Interruptor en serie**



Especificación	Ref.	UE	SP	EAN
 blanco brillante	2860 201	1/5	01	4010337065876
 blanco mate	2860 27	1/5	01	4010337029373
 antracita	2860 28	1/5	11	4010337029397
 color aluminio	2860 26	1/5	11	4010337029380
 negro mate	2860 005	1/5	11	4010337038023
 gris mate	2860 015	1/5	11	4010337087199
 acero inoxidable	2860 600	1/5	11	4010337021223

**Datos técnicos**

Profundidad de instalación

- 2860 ... 28 mm  
- 2861 ... 32 mm

Sección de conexión

- para conductores rígidos y flexibles de hasta: 2,5 mm<sup>2</sup>

Potencia nominal  
- LEDi/ CFLi:

100 W

---

## Notes

- Sujeto a disponibilidad.

---