

Bouton-poussoir 10 AX 250 V~ avec bascule droite avec fenêtre de contrôle Inverseur unipolaire



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc brillant	0120 201	1/5	20,63	11	4010337065982
 blanc satiné	0120 27	1/5	20,63	01	4010337029465
 anthracite	0120 28	1/5	21,37	11	4010337029489
 teinte alu	0120 26	1/5	24,57	11	4010337029472
 noir mat	0120 005	1/5	24,57	11	4010337037927
 acier inoxydable	0120 600	1/5	31,34	11	4010337021247

Caractéristiques techniques

Profondeur d'encastrement: 28 mm

section de raccordement
- pour conducteurs rigides et flexibles jusqu'à: 2,5mm²

Indications

- À raccorder aussi en éclairable.
