








Interrupteur-poussoir 10 AX 250 V~avec bascule droite Interrupteur permutateur



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc brillant	0123 201	1/5	28,29	01	4010337052708
 blanc satiné	0123 27	1/5	28,29	01	4010337029342
 anthracite	0123 28	1/5	28,85	11	4010337029366
 teinte alu	0123 26	1	32,03	11	4010337029359
 noir mat	0123 005	1	32,03	11	4010337037996
 gris mat	0123 015	1	32,03	11	4010337077114
 acier inoxydable	0123 600	1	39,06	11	4010337021254

Caractéristiques techniques

Profondeur d'encastrement:	28 mm
section de raccordement - pour conducteurs rigides et flexibles jusqu'à:	2,5mm ²
Puissance nominale - LEDi/ CFLi:	100 W

Indications

- A condition que la livraison soit possible.
