









## Interrupteur-poussoir 10 AX 250 V~ avec bascule 2x Interrupteur de série



| Spécification   | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|---|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 0125 01  | 1/5 | 28,37          | 01 | 4010337125013 |
|  blanc brillant      | 0125 03  | 1/5 | 28,37          | 01 | 4010337125037 |
|  blanc satiné        | 0125 27  | 1/5 | 28,37          | 01 | 4010337125273 |
|  anthracite          | 0125 28  | 1/5 | 28,88          | 11 | 4010337125280 |
|  teinte alu          | 0125 26  | 1/5 | 32,08          | 11 | 4010337125266 |
|  noir mat            | 0125 005 | 1/5 | 32,08          | 11 | 4010337038016 |
|  gris mat            | 0125 015 | 1/5 | 32,08          | 11 | 4010337077138 |
|  acier inoxydable    | 0125 600 | 1/5 | 39,15          | 11 | 4010337021780 |

### Caractéristiques techniques

Profondeur d'encastrement  
- 0125 ...: 28 mm

|  |                    |
|--|--------------------|
| - 0128 ...:  | 32 mm              |
| section de raccordement<br>- pour conducteurs rigides et flexibles<br>jusqu'à: | 2,5mm <sup>2</sup> |
| Puissance nominale<br>- LEDi/ CFLi:  | 100 W              |

---

## Indications

- A condition que la livraison soit possible.

---