

Interrupteur de série



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc	0125 40	1/5		01	4010337125402
 gris	0125 42	1/5		11	4010337125426
 Rouge	0125 43	1/5		11	4010337125433
 bleu	0125 46	1/5		11	4010337125464
 noir	0125 47	1/5		11	4010337125471

Caractéristiques techniques

Profondeur d'encastrement

- 0125 ...:	28 mm
- 0128 ...:	32 mm

section de raccordement

- pour conducteurs rigides et flexibles jusqu'à:	2,5mm ²
--	--------------------

Puissance nominale

- LEDi/ CFLi:	100 W
---------------	-------