











Interrupteur-poussoir 10 AX 250 V~ avec bascule
Interrupteur va-et-vient universel



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	0126 01	1/5	15,92	01	4010337126010
 blanc brillant	0126 03	10	15,92	01	4010337126034
 blanc satiné	0126 27	10	15,92	01	4010337126270
 anthracite	0126 28	10	16,37	11	4010337126287
 teinte alu	0126 26	1/5	19,25	11	4010337126263
 noir mat	0126 005	10	19,25	11	4010337037965
 gris mat	0126 015	1/5	19,25	11	4010337077145
 acier inoxydable	0126 600	1/5	25,56	11	4010337021742
 bronze	0126 603	1/5	25,30	11	4010337106043

Caractéristiques techniques

Profondeur d'encastrement:	28 mm
section de raccordement - pour conducteurs rigides et souples jusqu'à:	2,5 mm ²
Puissance nominale - LEDi/ CFLi:	100 W
