









Interrupteur-poussoir 10 AX 250 V~ avec bascule
Interrupteur va-et-vient universel



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|---|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 0126 01 | 1/5 | 17,70 | 01 | 4010337126010 |
|  blanc brillant | 0126 03 | 1/5 | 17,70 | 01 | 4010337126034 |
|  blanc satiné | 0126 27 | 1/5 | 17,70 | 01 | 4010337126270 |
|  anthracite | 0126 28 | 1/5 | 18,20 | 11 | 4010337126287 |
|  teinte alu | 0126 26 | 1/5 | 21,40 | 11 | 4010337126263 |
|  noir mat | 0126 005 | 1/5 | 21,40 | 11 | 4010337037965 |
|  gris mat | 0126 015 | 1/5 | 21,40 | 11 | 4010337077145 |
|  acier inoxydable | 0126 600 | 1/5 | 28,42 | 11 | 4010337021742 |

Caractéristiques techniques

Profondeur d'encastrement: 28 mm

section de raccordement
- pour conducteurs rigides et flexibles jusqu'à: 2,5mm²

Les illustrations sont similaires et peuvent différer de l'original.
Prix valables pour le pays : Belgique avec le prix actuel 01/24.

Puissance nominale
- LEDi/ CFLi:

100 W

Indications

- A condition que la livraison soit possible.
