

Interrupteur-poussoir 10 AX 250 V~ avec bascule
Interrupteur permutateur



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	0127 01	1/5	28,29	01	4010337127017
 blanc brillant	0127 03	1/5	28,29	01	4010337127031
 blanc satiné	0127 27	1/5	28,29	01	4010337127277
 anthracite	0127 28	1/5	28,85	11	4010337127284
 teinte alu	0127 26	1/5	32,03	11	4010337127260
 noir mat	0127 005	1/5	32,03	11	4010337037989
 gris mat	0127 015	1/5	32,03	11	4010337077169
 acier inoxydable	0127 600	1/5	39,06	11	4010337021759
 bronze	0127 603	1/5	38,27	11	4010337106067

Caractéristiques techniques

Profondeur d'encastrement: 28 mm

section de raccordement
- pour conducteurs rigides et flexibles jusqu'à: 2,5mm²

Puissance nominale
- LEDi/ CFLi: 100 W
