

Commutateur va-et-vient double



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc	0128 40	1/5		01	4010337128403
 gris	0128 42	1/5		11	4010337128427
 Rouge	0128 43	1/5		11	4010337128434
 bleu	0128 46	1/5		11	4010337128465
 noir	0128 47	1/5		11	4010337128472

Caractéristiques techniques

Profondeur d'encastrement

- 0125 ...:	28 mm
- 0128 ...:	32 mm

section de raccordement

- pour conducteurs rigides et flexibles jusqu'à:	2,5mm ²
--	--------------------

Puissance nominale

- LEDi/ CFLi:	100 W
---------------	-------