









Bouton-poussoir 10 A 250 V~ avec bascule droite Inverseur unipolaire



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc brillant	0130 201	1/5	19,18	01	4010337066064
 blanc satiné	0130 27	1/5	19,18	01	4010337029434
 anthracite	0130 28	1/5	19,91	11	4010337029458
 teinte alu	0130 26	1/5	23,08	11	4010337029441
 noir mat	0130 005	1/5	23,08	11	4010337037910
 gris mat	0130 015	1/5	23,08	11	4010337077183
 acier inoxydable	0130 600	1/5	29,95	11	4010337035947

Caractéristiques techniques

Profondeur d'encastrement:	28 mm
section de raccordement - pour conducteurs rigides et flexibles jusqu'à:	2,5mm ²

Indications

- A condition que la livraison soit possible.
