

Interrupteur-poussoir de commande 10 AX 250 V~ avec bascule
Interrupteur va-et-vient universel



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	0136 01	1/5	34,39	01	4010337136019
 blanc brillant	0136 03	1/5	34,39	01	4010337136033
 blanc satiné	0136 27	1/5	34,39	01	4010337136279
 anthracite	0136 28	1/5	34,92	11	4010337136286
 teinte alu	0136 26	1/5	38,04	11	4010337136262
 noir mat	0136 005	1/5	38,04	11	4010337037941
 gris mat	0136 015	1/5	38,04	11	4010337077190
 acier inoxydable	0136 600	1/5	45,16	11	4010337021766
 bronze	0136 603	1/5	44,07	11	4010337106081

Caractéristiques techniques

Profondeur d'encastrement:	28 mm
section de raccordement - pour conducteurs rigides et flexibles jusqu'à:	2,5mm ²
Puissance nominale - LEDi/ CFLi:	100 W

Indications

- À raccorder aussi en éclairable.

Etendue de la livraison

- L élément de lampe néon 230 V~, 1,5 mA est compris dans la livraison.
-