








## Cadre de finition Gira E2 noir mat



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 09	10	11,76	11	4010337036739
 1,5x	1001 09	10	17,40	11	4010337072775
 2x	0212 09	10	17,86	11	4010337036760
 2x sans nervure centrale	1002 09	10	17,86	11	4010337036784
 3x	0213 09	1/5	29,37	11	4010337036821
 4x	0214 09	1/5	47,70	11	4010337036869
 5x	0215 09	1	72,58	11	4010337036906

### Indications

- Convient également pour installations en goulotte.
- En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.