








Cadre de finition Gira E1 blanc brillant



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 150	10	7,49	01	4010337126119
 2x	0212 150	10	10,28	01	4010337126126
 2x sans nervure centrale	1002 150	10	10,28	01	4010337126133
 3x	0213 150	1/5	18,76	01	4010337126140
 4x	0214 150	1/5	30,30	01	4010337126157
 5x	0215 150	1/5	46,23	01	4010337126164

Caractéristiques

- Incassable.

Indications

- Convient également pour installations en goulotte.
- En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.