






## Cadre de finition Gira Esprit acier inoxydable



| Spécification  | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|--|----------|-----|----------------|----|---------------|
|  1x                        | 0211 219 | 1   | 48,85          | 11 | 4010337015765 |
|  2x                       | 0212 219 | 1   | 83,50          | 11 | 4010337015772 |
|  2x sans nervure centrale | 1002 219 | 1   | 83,50          | 11 | 4010337015802 |
|  3x                       | 0213 219 | 1   | 139,21         | 11 | 4010337015789 |
|  4x                       | 0214 219 | 1   | 192,26         | 11 | 4010337015796 |

### Caractéristiques

- Acier inoxydable brossé.