







## Cadre de finition Gira E2 blanc brillant



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 29	10/100	7,26	01	4010337211297
 2x	0212 29	10/100	9,96	01	4010337212294
 2x sans nervure centrale	1002 29	10	9,96	01	4010337001553
 3x	0213 29	1/5	18,18	01	4010337213291
 4x	0214 29	1/5	29,36	01	4010337214298
 5x	0215 29	1/5	44,80	01	4010337215295

### Indications

- Convient également pour installations en goulotte.
- En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.