







Cadre de finition Gira E2 acier inoxydable



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 33	10	19,13	11	4010337019794
 2x	0212 33	10	29,65	11	4010337019800
 2x sans nervure centrale	1002 33	10	29,65	11	4010337019848
 3x	0213 33	1/5	54,51	11	4010337019817
 4x	0214 33	1/5	84,59	11	4010337019824
 5x	0215 33	1/5	128,82	11	4010337019831

Indications

- Convient également pour installations en goulotte.
- En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.