








## Cadre de finition Gira E2 gris mat



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 37	10	8,95	11	4010337077299
 1,5x	1001 37	10	13,25	11	4010337082422
 2x	0212 37	10	13,60	11	4010337077589
 2x sans nervure centrale	1002 37	10	13,60	11	4010337082439
 3x	0213 37	1	22,35	11	4010337077602
 4x	0214 37	1	36,31	11	4010337077626
 5x	0215 37	1	55,25	11	4010337077640

### Caractéristiques

- Incassable.

## Indications

- Convient également pour installations en goulotte.
  - En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour l'installation encastrée protégée contre l'eau IP44.
-