







Cadre de finition Gira Standard 55 blanc crème brillant



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 01	10/100	3,09	21	4010337211013
 2x	0212 01	10/100	5,28	21	4010337212010
 2x sans nervure centrale	1002 01	10	3,90	01	4010337002017
 3x	0213 01	10/100	9,31	01	4010337213017
 4x	0214 01	1/5	16,10	01	4010337214014
 5x	0215 01	1/5	26,48	01	4010337215011

Caractéristiques

- Incassable.

Indications

- Convient également pour installations en goulotte.
- En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.