








Cadre de finition Gira E2 noir mat



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|---------|-----|----------------|----|---------------|
|  1x | 0211 09 | 10 | 11,76 | 11 | 4010337036739 |
|  1,5x | 1001 09 | 10 | 17,40 | 11 | 4010337072775 |
|  2x | 0212 09 | 10 | 17,86 | 11 | 4010337036760 |
|  2x sans nervure centrale | 1002 09 | 10 | 17,86 | 11 | 4010337036784 |
|  3x | 0213 09 | 1/5 | 29,37 | 11 | 4010337036821 |
|  4x | 0214 09 | 1/5 | 47,70 | 11 | 4010337036869 |
|  5x | 0215 09 | 1 | 72,58 | 11 | 4010337036906 |

Indications

- Convient également pour installations en goulotte.
- En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.