







## Cadre de finition Gira F100 blanc brillant



| Spécification  | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|--|----------|-----|----------------|----|---------------|
|  1x                        | 0211 112 | 10  | 7,56           | 01 | 4010337043973 |
|  2x                       | 0212 112 | 10  | 13,34          | 01 | 4010337044017 |
|  2x sans nervure centrale | 1002 112 | 10  | 13,34          | 01 | 4010337047094 |
|  3x                       | 0213 112 | 1/5 | 21,54          | 01 | 4010337044031 |
|  4x                       | 0214 112 | 1/5 | 34,67          | 01 | 4010337044055 |
|  5x                       | 0215 112 | 1/5 | 52,96          | 01 | 4010337044079 |

### Caractéristiques

- Incassable.

### Indications

- En combinaison avec la bride d'étanchéité, convient également à un montage encastré protégé contre l'eau IP44.