






Cadre de finition Gira Esprit aluminium (anodisé)



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|---------|-----|----------------|----|---------------|
|  1x | 0211 17 | 1 | 44,38 | 11 | 4010337211174 |
|  2x | 0212 17 | 1 | 75,90 | 11 | 4010337212171 |
|  2x sans nervure centrale | 1002 17 | 1 | 75,90 | 11 | 4010337002178 |
|  3x | 0213 17 | 1 | 126,55 | 11 | 4010337213178 |
|  4x | 0214 17 | 1 | 174,80 | 11 | 4010337214175 |

Caractéristiques

- Aluminium anodisé E 1 EV 1.