







## Cadre de finition Gira E2 anthracite



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 23	10/100	7,86	11	4010337211235
 2x	0212 23	10/100	11,36	11	4010337212232
 2x sans nervure centrale	1002 23	10	11,36	11	4010337002239
 3x	0213 23	1/5	19,67	11	4010337213239
 4x	0214 23	1/5	31,69	11	4010337214236
 5x	0215 23	1/5	48,31	11	4010337215233

### Indications

- Convient également pour installations en goulotte.
- En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.