







## Cadre de finition Gira E2 teinte alu



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 25	10/100	11,76	11	4010337211259
 2x	0212 25	10	17,86	11	4010337212256
 2x sans nervure centrale	1002 25	10	17,86	11	4010337002253
 3x	0213 25	1/5	29,37	11	4010337213253
 4x	0214 25	1/5	47,70	11	4010337214250
 5x	0215 25	1/5	72,58	11	4010337215257

### Indications

- Convient également pour installations en goulotte.
- En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.