







## Cadre de finition Gira F100 blanc brillant



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 112	10	7,56	01	4010337043973
 2x	0212 112	10	13,34	01	4010337044017
 2x sans nervure centrale	1002 112	10	13,34	01	4010337047094
 3x	0213 112	1/5	21,54	01	4010337044031
 4x	0214 112	1/5	34,67	01	4010337044055
 5x	0215 112	1/5	52,96	01	4010337044079

### Caractéristiques

- Incassable.

### Indications

- En combinaison avec la bride d'étanchéité, convient également à un montage encastré protégé contre l'eau IP44.