







Cadre de finition Gira E1 anthracite



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|----------|-----|----------------|----|---------------|
|  1x | 0211 152 | 10 | 7,86 | 11 | 4010337125969 |
|  2x | 0212 152 | 10 | 11,36 | 11 | 4010337125976 |
|  2x sans nervure centrale | 1002 152 | 1 | 11,36 | 11 | 4010337125983 |
|  3x | 0213 152 | 1/5 | 19,67 | 11 | 4010337125990 |
|  4x | 0214 152 | 1/5 | 31,69 | 11 | 4010337126027 |
|  5x | 0215 152 | 1/5 | 48,31 | 11 | 4010337126041 |

Caractéristiques

- Incassable.

Indications

- Convient également pour installations en goulotte.
- En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.