









## Bascule avec symbole Porte



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	0287 01	10	5,65	01	4010337287018
 blanc brillant	0287 03	10	5,65	01	4010337287032
 blanc satiné	0287 27	10	5,65	01	4010337287278
 anthracite	0287 28	1	6,14	11	4010337287285
 teinte alu	0287 26	1	9,29	11	4010337287261
 noir mat	0287 005	1	9,29	11	4010337038283
 gris mat	0287 015	1	9,29	11	4010337079637
 acier inoxydable	0287 600	1	16,40	11	4010337021704

## Indications

- A condition que la livraison soit possible.