










## Bascule avec fenêtre de contrôle



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	0290 01	10	5,64	01	4010337290018
 blanc brillant	0290 03	10/100	5,64	01	4010337290032
 blanc satiné	0290 27	10	5,64	01	4010337290278
 anthracite	0290 28	10	6,14	11	4010337290285
 teinte alu	0290 26	10	9,29	11	4010337290261
 noir mat	0290 005	10	9,29	11	4010337038184
 gris mat	0290 015	10	9,29	11	4010337079996
 acier inoxydable	0290 600	10	16,37	11	4010337021674