









## Bascule 2x avec symbole de flèche



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	0294 01	10	10,50	01	4010337294016
 blanc brillant	0294 03	10/100	10,50	01	4010337294030
 blanc satiné	0294 27	10	10,50	01	4010337294276
 anthracite	0294 28	10	11,06	11	4010337294283
 teinte alu	0294 26	10	14,24	11	4010337294269
 noir mat	0294 005	10	14,68	11	4010337038108
 gris mat	0294 015	10	14,68	11	4010337080206
 acier inoxydable	0294 600	10	21,28	11	4010337021735

### Indications

- A condition que la livraison soit possible.