

Bouton à bascule



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|----------|--------|----------------|----|---------------|
|  blanc crème brillant | 0296 01 | 10 | 4,03 | 21 | 4010337296010 |
|  blanc brillant | 0296 03 | 10/100 | 4,03 | 21 | 4010337296034 |
|  blanc satiné | 0296 27 | 10/100 | 4,03 | 21 | 4010337296270 |
|  anthracite | 0296 28 | 10/100 | 4,74 | 11 | 4010337296287 |
|  teinte alu | 0296 26 | 10 | 7,93 | 11 | 4010337296263 |
|  noir mat | 0296 005 | 10 | 7,93 | 11 | 4010337038061 |
|  gris mat | 0296 015 | 10 | 7,93 | 11 | 4010337080220 |
|  acier inoxydable | 0296 600 | 10 | 14,96 | 11 | 4010337021667 |
|  bronze | 0296 603 | 10 | 15,59 | 11 | 4010337097747 |

Indications

- Cadre de finition (1x à 5x) des programmes d'interrupteurs Standard 55 et Gira E2, en combinaison avec le kit d'étanchéité, convient également à l'installation d'interrupteurs à bascule et de boutons-poussoirs à bascule, avec indice de protection IP44 (protection contre l'eau) (ne s'applique pas à la bascule 2x).
