









## Bascule avec zone d'inscription



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	0299 01	10	7,97	01	4010337299011
 blanc brillant	0299 03	10	7,97	01	4010337299035
 blanc satiné	0299 27	10	7,97	01	4010337299271
 anthracite	0299 28	10	8,48	11	4010337299288
 teinte alu	0299 26	1	11,63	11	4010337299264
 noir mat	0299 005	1	11,63	11	4010337038122
 gris mat	0299 015	1	11,63	11	4010337080718
 acier inoxydable	0299 600	1	18,71	11	4010337021711

## Indications

- A condition que la livraison soit possible.

## Etendue de la livraison

- Étiquette vierge fournie.
  - Les étiquettes avec les symboles « lumière », « sonnette » et « porte » sont fournies.
-