









## Bascule avec zone d'inscription



| Spécification  | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|--|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 0299 01  | 10  | 7,97           | 01 | 4010337299011 |
|  blanc brillant     | 0299 03  | 10  | 7,97           | 01 | 4010337299035 |
|  blanc satiné       | 0299 27  | 10  | 7,97           | 01 | 4010337299271 |
|  anthracite         | 0299 28  | 10  | 8,48           | 11 | 4010337299288 |
|  teinte alu         | 0299 26  | 1   | 11,63          | 11 | 4010337299264 |
|  noir mat           | 0299 005 | 1   | 11,63          | 11 | 4010337038122 |
|  gris mat           | 0299 015 | 1   | 11,63          | 11 | 4010337080718 |
|  acier inoxydable   | 0299 600 | 1   | 18,71          | 11 | 4010337021711 |

## Etendue de la livraison

- Étiquette vierge fournie.
- Les étiquettes avec les symboles « lumière », « sonnette » et « porte » sont fournies.