








Bascule avec fenêtre de contrôle et zone d'inscription



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	0670 01	1	9,29	01	4010337670018
 blanc brillant	0670 03	10	9,29	01	4010337670032
 blanc satiné	0670 27	10	9,29	01	4010337670278
 anthracite	0670 28	1	9,88	11	4010337670285
 teinte alu	0670 26	1	13,03	11	4010337670261
 noir mat	0670 005	1	13,03	11	4010337038191
 gris mat	0670 015	1	13,03	11	4010337081708

Indications

- A condition que la livraison soit possible.

Etendue de la livraison

- Les étiquettes avec les symboles « lumière », « sonnette » et « porte » sont fournies.
