








Bascule avec fenêtre de contrôle et zone d'inscription



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 0670 01 | 1 | 9,29 | 01 | 4010337670018 |
|  blanc brillant | 0670 03 | 10 | 9,29 | 01 | 4010337670032 |
|  blanc satiné | 0670 27 | 10 | 9,29 | 01 | 4010337670278 |
|  anthracite | 0670 28 | 1 | 9,88 | 11 | 4010337670285 |
|  teinte alu | 0670 26 | 1 | 13,03 | 11 | 4010337670261 |
|  noir mat | 0670 005 | 1 | 13,03 | 11 | 4010337038191 |
|  gris mat | 0670 015 | 1 | 13,03 | 11 | 4010337081708 |

Indications

- A condition que la livraison soit possible.

Etendue de la livraison

- Les étiquettes avec les symboles « lumière », « sonnette » et « porte » sont fournies.
