








## Bascule avec fenêtre de contrôle et zone d'inscription



| Spécification  | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|--|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 0670 01  | 1   | 9,29           | 01 | 4010337670018 |
|  blanc brillant     | 0670 03  | 10  | 9,29           | 01 | 4010337670032 |
|  blanc satiné       | 0670 27  | 10  | 9,29           | 01 | 4010337670278 |
|  anthracite         | 0670 28  | 1   | 9,88           | 11 | 4010337670285 |
|  teinte alu         | 0670 26  | 1   | 13,03          | 11 | 4010337670261 |
|  noir mat           | 0670 005 | 1   | 13,03          | 11 | 4010337038191 |
|  gris mat           | 0670 015 | 1   | 13,03          | 11 | 4010337081708 |

### Indications

- A condition que la livraison soit possible.

## Etendue de la livraison

- Les étiquettes avec les symboles « lumière », « sonnette » et « porte » sont fournies.

---