








## Bascule avec symbole sonnette et zone d'inscription Sonnette



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	0673 01	1	9,31	01	4010337673019
 blanc brillant	0673 03	10	9,31	01	4010337673033
 blanc satiné	0673 27	10	9,31	01	4010337673279
 anthracite	0673 28	1	9,89	11	4010337673286
 teinte alu	0673 26	1	13,05	11	4010337673262
 noir mat	0673 005	1	13,05	11	4010337038269
 gris mat	0673 015	1	13,05	11	4010337081715

### Indications

- A condition que la livraison soit possible.

## Etendue de la livraison

- Étiquette vierge fournie.

---