


**Prise sans contact de mise à la terre
à 2 pôles 16 A 250 V~
sans shutter**



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc	0980 40	1		01	4010337980407
 gris	0980 42	1		11	4010337980421
 Rouge	0980 43	1		11	4010337980438
 bleu	0980 46	1		11	4010337980469
 noir	0980 47	1		11	4010337980476

Caractéristiques techniques

section de raccordement
- Pour les conducteurs de:

1,5 mm² à 2,5 mm²