








Cadre de finition Gira E2 gris mat



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|---------|-----|----------------|----|---------------|
|  1x | 0211 37 | 10 | 11,76 | 11 | 4010337077299 |
|  1,5x | 1001 37 | 10 | 17,40 | 11 | 4010337082422 |
|  2x | 0212 37 | 10 | 17,86 | 11 | 4010337077589 |
|  2x sans nervure centrale | 1002 37 | 10 | 17,86 | 11 | 4010337082439 |
|  3x | 0213 37 | 1 | 29,37 | 11 | 4010337077602 |
|  4x | 0214 37 | 1 | 47,70 | 11 | 4010337077626 |
|  5x | 0215 37 | 1 | 72,58 | 11 | 4010337077640 |

Indications

- Convient également pour installations en goulotte.
- En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.