








## Bascule 2x avec symboles de flèche



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	1150 01	1	10,50	01	4010337150015
 blanc brillant	1150 03	1	10,50	01	4010337150039
 blanc satiné	1150 27	1	10,50	01	4010337150275
 anthracite	1150 28	1	11,06	11	4010337150282
 teinte alu	1150 26	1	14,24	11	4010337150268
 noir mat	1150 005	1	14,24	11	4010337038115
 gris mat	1150 015	1	14,24	11	4010337082897