








## Bascule 2x avec symboles de flèche



| Spécification  | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|--|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 1150 01  | 1   | 10,50          | 01 | 4010337150015 |
|  blanc brillant     | 1150 03  | 1   | 10,50          | 01 | 4010337150039 |
|  blanc satiné       | 1150 27  | 1   | 10,50          | 01 | 4010337150275 |
|  anthracite         | 1150 28  | 1   | 11,06          | 11 | 4010337150282 |
|  teinte alu         | 1150 26  | 1   | 14,24          | 11 | 4010337150268 |
|  noir mat           | 1150 005 | 1   | 14,24          | 11 | 4010337038115 |
|  gris mat           | 1150 015 | 1   | 14,24          | 11 | 4010337082897 |

### Indications

- A condition que la livraison soit possible.