










Cache avec cache rapporté pour module rapporté détecteur de mouvement 1,10 m Standard



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	1470 01	1	5,10	02	4010337020967
 blanc brillant	1470 03	1	5,10	02	4010337020974
 teinte alu	1470 26	1	13,55	02	4010337030010
 blanc satiné	1470 27	1	5,10	02	4010337075257
 anthracite	1470 28	1	8,44	02	4010337075264
 teinte alu	1470 65	1	31,52	02	4010337075516
 blanc	1470 66	1	23,03	02	4010337075523
 anthracite	1470 67	1	31,52	02	4010337075530
 blanc brillant	1470 112	1	8,65	02	4010337075240

