










Cache avec cache rapporté pour module rapporté détecteur de mouvement 1,10 m Standard



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 1470 01 | 1 | 5,10 | 02 | 4010337020967 |
|  blanc brillant | 1470 03 | 1 | 5,10 | 02 | 4010337020974 |
|  teinte alu | 1470 26 | 1 | 13,55 | 02 | 4010337030010 |
|  blanc satiné | 1470 27 | 1 | 5,10 | 02 | 4010337075257 |
|  anthracite | 1470 28 | 1 | 8,44 | 02 | 4010337075264 |
|  teinte alu | 1470 65 | 1 | 31,52 | 02 | 4010337075516 |
|  blanc | 1470 66 | 1 | 23,03 | 02 | 4010337075523 |
|  anthracite | 1470 67 | 1 | 31,52 | 02 | 4010337075530 |
|  blanc brillant | 1470 112 | 1 | 8,65 | 02 | 4010337075240 |

