









## Jeu de bascules 4x (1+3)



| Spécification  | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|--|----------|-----|----------------|----|---------------|
|  blanc crème brillant (laqué) | 2184 01  | 1   | 38,71          | 06 | 4010337012184 |
|  blanc brillant (laqué)     | 2184 03  | 1   | 38,71          | 06 | 4010337012191 |
|  blanc satiné (laqué)       | 2184 27  | 1   | 38,71          | 06 | 4010337013396 |
|  anthracite (laqué)         | 2184 28  | 1   | 42,10          | 06 | 4010337012207 |
|  teinte alu (laqué)         | 2184 26  | 1   | 45,95          | 06 | 4010337012214 |
|  noir mat (laqué)           | 2184 005 | 1   | 45,95          | 06 | 4010337038412 |
|  gris mat (laqué)           | 2184 015 | 1   | 45,95          | 06 | 4010337083474 |
|  acier inoxydable           | 2134 601 | 1   | 28,55          | 06 | 4010337020226 |

### Indications

- Les jeux de bascules inscriptibles et de bascules sans zone d'inscription sont en métal, ce qui peut réduire la portée en cas d'utilisations radio.