










## Jeu de bascules 2x Plus



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant (laqué)	2192 01	1	30,99	06	4010337012269
 blanc pur brillant (laqué)	2192 03	1	30,99	06	4010337012276
 blanc pur satiné (laqué)	2192 27	1	30,99	06	4010337013419
 anthracite (laqué)	2192 28	1	35,15	06	4010337012283
 teinte alu (laqué)	2192 26	1	38,26	06	4010337012290
 noir mat (vernis)	2192 005	1	38,26	06	4010337038351
 gris mat (vernis)	2192 015	1	38,26	06	4010337083832
 acier inoxydable	2142 601	1	25,71	06	4010337020141

### Indications

- Les jeux de bascules inscriptibles et de bascules sans zone d'inscription sont en métal, ce qui peut réduire la portée en cas d'utilisations radio.