











Haut-parleurs pour radio encastrée



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	2282 01	1	27,64	03	4010337076230
 blanc brillant	2282 03	1	27,64	03	4010337076247
 blanc satiné	2282 27	1	27,64	03	4010337076254
 anthracite	2282 28	1	29,76	03	4010337076261
 teinte alu	2282 26	1	32,42	03	4010337076162
 en optique verre noir	2282 05	1	37,20	03	4010337889182
 noir mat	2282 005	1	32,42	03	4010337037286
 gris mat	2282 015	1	32,42	03	4010337083931
 acier inoxydable	2282 600	1	37,20	03	4010337032861

Caractéristiques

- Haut-parleurs pour le raccordement à la radio encastrée Gira.

Caractéristiques techniques

Profondeur de montage:	32 mm
section de raccordement - Raccordement haut-parleur/AUX:	1,5mm ²
Impédance:	8 Ω
Température ambiante:	-5°C à +50°C
