











Haut-parleurs pour radio encastrée



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|---|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 2282 01 | 1 | 26,73 | 03 | 4010337076230 |
|  blanc brillant | 2282 03 | 1 | 26,73 | 03 | 4010337076247 |
|  blanc satiné | 2282 27 | 1 | 26,73 | 03 | 4010337076254 |
|  anthracite | 2282 28 | 1 | 28,78 | 03 | 4010337076261 |
|  teinte alu | 2282 26 | 1 | 31,35 | 03 | 4010337076162 |
|  en optique verre noir | 2282 05 | 1 | 35,98 | 03 | 4010337889182 |
|  noir mat | 2282 005 | 1 | 31,35 | 03 | 4010337037286 |
|  gris mat | 2282 015 | 1 | 31,35 | 03 | 4010337083931 |
|  acier inoxydable | 2282 600 | 1 | 35,98 | 03 | 4010337032861 |

Caractéristiques

- Haut-parleurs pour le raccordement à la radio encastrée Gira.

Caractéristiques techniques

| | |
|---|--------------------|
| Profondeur d'encastrement: | 32 mm |
| section de raccordement - Raccordement haut-parleur/AUX: | 1,5mm ² |
| Impédance: | 8 Ω |
| Température ambiante: | -5°C à +50°C |
