









Cache pour haut-parleur



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	2483 01	1	5,35	03	4010337483014
 blanc brillant	2483 03	1	4,93	03	4010337483038
 en optique verre noir	2483 05	1	10,91	03	4010337079781
 blanc satiné	2483 27	1	5,35	03	4010337483274
 anthracite	2483 28	1	8,01	03	4010337483281
 teinte alu	2483 26	1	11,81	03	4010337483267
 noir mat	2483 005	1	11,81	03	4010337129417
 gris mat	2483 015	1	11,81	03	4010337129424
 acier inoxydable	2483 600	1	16,44	03	4010337129431

