









Cache avec sortie oblique 30° et zone d'inscription pour anneau de support jack modulaire 2x



| Spécification  | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|--|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 2640 01  | 10  | 8,29           | 01 | 4010337460114 |
|  blanc brillant     | 2640 03  | 10  | 8,29           | 01 | 4010337460138 |
|  blanc satiné       | 2640 27  | 10  | 8,29           | 01 | 4010337460183 |
|  anthracite         | 2640 28  | 10  | 10,95          | 11 | 4010337460190 |
|  teinte alu         | 2640 26  | 10  | 14,95          | 11 | 4010337460176 |
|  noir mat           | 2640 005 | 10  | 14,95          | 11 | 4010337036500 |
|  gris mat           | 2640 015 | 10  | 14,95          | 11 | 4010337085195 |
|  acier inoxydable   | 2640 600 | 10  | 18,83          | 11 | 4010337021582 |

#### Etendue de la livraison

- Étiquette vierge fournie.