










Cache avec sortie oblique 30° et zone d'inscription pour anneau de support jack modulaire 2x



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	2640 01	10	8,56	01	4010337460114
 blanc brillant	2640 03	10	8,56	01	4010337460138
 blanc satiné	2640 27	10	8,56	01	4010337460183
 anthracite	2640 28	10	11,30	11	4010337460190
 teinte alu	2640 26	10	15,43	11	4010337460176
 noir mat	2640 005	10	15,43	11	4010337036500
 gris mat	2640 015	10	15,43	11	4010337085195
 acier inoxydable	2640 600	10	19,43	11	4010337021582

Etendue de la livraison

- Étiquette vierge fournie.